

# SERVICE MANUAL

SKANTIC

LUXOR

8010



## TYPE 130 9302

### DATA

Driftspänning	Mains voltage	Betriebsspannung	220 - 240 V, 50 Hz
Hastigheter	Speeds	Geschwindigkeit	33 1/3 and 45 v/min $\pm$ 1,0%
Finjustering	Pitch control range	Feinjustierung	33 1/3 $\pm$ 4,0% and 45 $\pm$ 5,0%
Nålkraft	Stylus force	Nadelaufkraft	0 - 35 mN (0 - 3,5p)
Frekvensområde	Frequency range	Frequenzbereich	20 - 20 000 $\pm$ 3,5 dB
Rekommenderad belastningsimpedans	Recommended load impedance	Empfohlene Belastungsimpedanz	47 k $\Omega$
Kanalisolering	Channel separation	Kanaltrennung	20 dB
Kanalbalans	Channel balance	Kanalbalance	2 dB
Känslighet	Sensitivity	Empfindlichkeit	1 mV/cm/s
Eftergivlighet	Compliance (hor. and vert.)	Nachgiebigkeit	20 $\mu$ m/mN
Svajning	Wow and flutter	Tonhöenschwankung	$\pm$ 0,1 %
Störavstånd, B-kurva	Signal/noise ratio, B-curve	Störabstand, B-Kurve	68 dB
Effektiv nålmasa	Effective stylus mass	Effektive Nadelmasse	0,8 mg
Frekvensintermod. (FIM)	Frequency intermod. (FIM)	Frequenzintermodulation (FIM)	1 %
Tonarmsresonans	Pick-up arm resonance	Tonarmresonanz	12 Hz
Vertikal spårinkel	Vertical tracking angle	Vertikaler Spurwinkel	20 $^{\circ}$

